

The tests have been made with a pressure of approx. 4 bar and a viscosity of 1 cSt (water).

If the viscosity is higher, you need a nozzle with a higher hole diameter.

The concentration is a guidance, as the viscosity will be decisive. See the product manual for further details!

* Included in nozzle set Art. No. 9378.

	Colour	Hole Diameter	Approx. % conc.	Approx. conc.
	* Transparent	No Tip	0,0 %	
	* Grey	3,250 m/m	10,0 %	1:10
	* Black	2,490 m/m	8,3 %	1:12
	* Beige	1,780 m/m	7,1 %	1:14
	* Red	1,320 m/m	6,3 %	1:16
	* White	1,090 m/m	5,6 %	1:18
	* Blue	1,020 m/m	4,8 %	1:21
	* Light brown	0,890 m/m	4,4 %	1:23
	* Green	0,710 m/m	3,0 %	1:33
	* Orange	0,640 m/m	2,5 %	1:40
	* Brown	0,580 m/m	2,2 %	1:45
	* Yellow	0,510 m/m	1,8 %	1:57
	* Turquoise	0,460 m/m	1,4 %	1:71
	* Purple	0,360 m/m	1,0 %	1:100
	* Pink	0,254 m/m	0,4 %	1:250